

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251311

Luminaire Tested: P3AS05R559030DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559030DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 666.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251311

CATALOG NUMBER: P3AS05R559030DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1251311

CATALOG NUMBER: P3AS05R559030DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94	92	90	89
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90	87	85	84
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		86	83	80	79
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82	78	76	74
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78	74	72	70
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74	70	68	66
8	83	74	69	65	82	74	69	65	73	68	65		72	67	64		71	67	64	63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68	64	61	60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184722
5°	183006
10°	190355
15°	187720
20°	173102
25°	140839
30°	85557
35°	29607
40°	8444
45°	4031
50°	1706
55°	765
60°	877
65°	778
70°	641
75°	847
80°	631
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4031 cd/sqm

TEST NUMBER: P1251311

CATALOG NUMBER: P3AS05R559030DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	12.1
10°-20°	229.8	34.5
20°-30°	256.2	38.5
30°-40°	83.8	12.6
40°-50°	11.0	1.7
50°-60°	2.3	0.4
60°-70°	1.4	0.2
70°-80°	0.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	566.4	85.0
0°-40°	650.2	97.6
0°-60°	663.6	99.6
0°-90°	666.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	842	
5°	831	80
15°	827	230
25°	582	256
35°	111	84
45°	13	11
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1251311

CATALOG NUMBER: P3AS05R559030DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	842.4
2.5°	836.4
5°	831.4
7.5°	843.4
10°	854.9
12.5°	848.9
15°	826.9
17.5°	791.8
20°	741.8
22.5°	672.7
25°	582.1
27.5°	467.0
30°	337.9
32.5°	207.2
35°	110.6
37.5°	56.1
40°	29.5
42.5°	19.0
45°	13.0
47.5°	9.0
50°	5.0
52.5°	3.0
55°	2.0
57.5°	2.0
60°	2.0
62.5°	1.5
65°	1.5
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)