

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251315

Luminaire Tested: P3AS05R559030DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559030DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 645.9 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251315
CATALOG NUMBER: P3AS05R559030DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1251315
 CATALOG NUMBER: P3AS05R559030DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187331
5°	180695
10°	187171
15°	184519
20°	170768
25°	138105
30°	82772
35°	28054
40°	7729
45°	3411
50°	989
55°	191
60°	88
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3411 cd/sqm



TEST NUMBER: P1251315
 CATALOG NUMBER: P3AS05R559030DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.4	12.3
10°-20°	226.3	35.0
20°-30°	251.6	38.9
30°-40°	78.3	12.1
40°-50°	9.4	1.5
50°-60°	0.7	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.3	86.3
0°-40°	635.6	98.4
0°-60°	645.7	100.0
0°-90°	645.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	645.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	854	
5°	821	79
15°	813	226
25°	571	252
35°	105	78
45°	11	9
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1251315
CATALOG NUMBER: P3AS05R559030DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	854.3
1°	851.1
2°	842.8
3°	832.5
4°	823.1
5°	820.9
6°	823.4
7°	828.5
8°	834.4
9°	839.1
10°	840.6
11°	839.6
12°	835.7
13°	829.5
14°	822.4
15°	812.8
16°	801.8
17°	787.8
18°	772.1
19°	753.2
20°	731.8
21°	707.5
22°	678.8
23°	647.2
24°	610.8
25°	570.8
26°	526.9
27°	480.3
28°	430.5
29°	379.2
30°	326.9
31°	274.4
32°	223.1
32.5°	200.3
33°	176.7
34°	136.7
35°	104.8
36°	79.8
37°	59.1
37.5°	50.6
38°	43.9
39°	33.4
40°	27.0
42.5°	17.2
45°	11.0



TEST NUMBER: P1251315
CATALOG NUMBER: P3AS05R559030DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.6
50°	2.9
52.5°	1.0
55°	0.5
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)