

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250115

Luminaire Tested: P3AS20R559027D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559027D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2036.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250115
CATALOG NUMBER: P3AS20R559027D010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1250115
 CATALOG NUMBER: P3AS20R559027D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79	79
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	590413
5°	569512
10°	589880
15°	581570
20°	538230
25°	435291
30°	260876
35°	88419
40°	24360
45°	10792
50°	3173
55°	573
60°	351
65°	415
70°	513
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10792 cd/sqm



TEST NUMBER: P1250115
 CATALOG NUMBER: P3AS20R559027D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.3	12.3
10°-20°	713.2	35.0
20°-30°	792.8	38.9
30°-40°	246.8	12.1
40°-50°	29.6	1.5
50°-60°	2.3	0.1
60°-70°	0.8	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1756.4	86.3
0°-40°	2003.2	98.4
0°-60°	2035.1	100.0
0°-90°	2036.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2036.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2692	
5°	2587	250
15°	2562	713
25°	1799	793
35°	330	247
45°	35	30
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1250115
CATALOG NUMBER: P3AS20R559027D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2692.5
1°	2682.5
2°	2656.2
3°	2623.7
4°	2594.3
5°	2587.3
6°	2595.1
7°	2611.3
8°	2629.9
9°	2644.6
10°	2649.2
11°	2646.1
12°	2633.7
13°	2614.4
14°	2592.0
15°	2561.8
16°	2527.0
17°	2482.9
18°	2433.4
19°	2373.8
20°	2306.5
21°	2230.0
22°	2139.5
23°	2039.7
24°	1925.2
25°	1799.1
26°	1660.7
27°	1513.7
28°	1356.7
29°	1195.0
30°	1030.3
31°	864.8
32°	703.1
32.5°	631.2
33°	556.9
34°	430.8
35°	330.3
36°	251.4
37°	186.4
37.5°	159.3
38°	138.5
39°	105.2
40°	85.1
42.5°	54.1
45°	34.8



TEST NUMBER: P1250115
CATALOG NUMBER: P3AS20R559027D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	20.9
50°	9.3
52.5°	3.1
55°	1.5
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)