

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250128

Luminaire Tested: P3AS20R559027D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559027D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1336.0 lumens
Efficiency: N/A
Efficacy: 46.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250128

CATALOG NUMBER: P3AS20R559027D010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250128

CATALOG NUMBER: P3AS20R559027D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	251208
5°	247985
10°	238205
15°	222816
20°	203251
25°	181341
30°	158607
35°	131785
40°	103880
45°	70457
50°	43052
55°	22327
60°	20744
65°	19665
70°	18208
75°	16013
80°	15911
85°	11825

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 70457 cd/sqm

TEST NUMBER: P1250128

CATALOG NUMBER: P3AS20R559027D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	7.9
10°-20°	274.3	20.5
20°-30°	343.5	25.7
30°-40°	306.6	23.0
40°-50°	179.6	13.4
50°-60°	62.0	4.6
60°-70°	37.5	2.8
70°-80°	20.8	1.6
80°-90°	6.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.5	54.2
0°-40°	1030.1	77.1
0°-60°	1271.7	95.2
0°-90°	1336.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1336.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1146	
5°	1127	106
15°	982	274
25°	750	344
35°	492	307
45°	227	180
55°	58	62
65°	38	37
75°	19	21
85°	5	6
90°	0	

TEST NUMBER: P1250128

CATALOG NUMBER: P3AS20R559027D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1145.6
2.5°	1139.3
5°	1126.6
7.5°	1101.4
10°	1069.8
12.5°	1030.4
15°	981.5
17.5°	929.4
20°	871.0
22.5°	811.1
25°	749.5
27.5°	688.0
30°	626.4
32.5°	560.2
35°	492.3
37.5°	426.0
40°	362.9
42.5°	295.1
45°	227.2
47.5°	173.6
50°	126.2
52.5°	82.1
55°	58.4
57.5°	52.1
60°	47.3
62.5°	42.6
65°	37.9
67.5°	33.1
70°	28.4
72.5°	23.7
75°	18.9
77.5°	15.8
80°	12.6
82.5°	7.9
85°	4.7
87.5°	3.2
90°	0.0

(END OF REPORT)