

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250131

Luminaire Tested: P3AS20R559027D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250131
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559027D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1148.0 lumens
Efficiency: N/A
Efficacy: 39.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250131

CATALOG NUMBER: P3AS20R559027D010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1250131

CATALOG NUMBER: P3AS20R559027D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	312300
5°	304468
10°	283050
15°	252056
20°	214195
25°	172849
30°	131792
35°	93719
40°	61859
45°	36686
50°	21526
55°	13266
60°	11753
65°	10637
70°	9104
75°	8049
80°	7956
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36686 cd/sqm

TEST NUMBER: P1250131

CATALOG NUMBER: P3AS20R559027D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	11.2
10°-20°	307.8	26.8
20°-30°	326.0	28.4
30°-40°	220.3	19.2
40°-50°	96.5	8.4
50°-60°	34.6	3.0
60°-70°	20.3	1.8
70°-80°	10.6	0.9
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.3	66.4
0°-40°	982.6	85.6
0°-60°	1113.7	97.0
0°-90°	1148.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1148.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1424	
5°	1383	128
15°	1110	308
25°	714	326
35°	350	220
45°	118	97
55°	35	35
65°	20	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1250131

CATALOG NUMBER: P3AS20R559027D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1424.2
2.5°	1413.1
5°	1383.2
7.5°	1334.3
10°	1271.2
12.5°	1195.5
15°	1110.3
17.5°	1015.7
20°	917.9
22.5°	815.4
25°	714.4
27.5°	615.1
30°	520.5
32.5°	430.6
35°	350.1
37.5°	277.6
40°	216.1
42.5°	162.4
45°	118.3
47.5°	86.7
50°	63.1
52.5°	44.2
55°	34.7
57.5°	31.5
60°	26.8
62.5°	23.7
65°	20.5
67.5°	17.3
70°	14.2
72.5°	12.6
75°	9.5
77.5°	7.9
80°	6.3
82.5°	4.7
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)