

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251366

Luminaire Tested: P3AS05R609030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251366
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 364.0 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251366

CATALOG NUMBER: P3AS05R609030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251366

CATALOG NUMBER: P3AS05R609030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92251
5°	90182
10°	84434
15°	75733
20°	65129
25°	53858
30°	42564
35°	31614
40°	21755
45°	13645
50°	7505
55°	4396
60°	3947
65°	3373
70°	2885
75°	2965
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13645 cd/sqm

TEST NUMBER: P1251366

CATALOG NUMBER: P3AS05R609030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.1	10.5
10°-20°	92.7	25.5
20°-30°	101.6	27.9
30°-40°	74.1	20.3
40°-50°	35.0	9.6
50°-60°	11.5	3.1
60°-70°	6.5	1.8
70°-80°	3.5	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.4	63.9
0°-40°	306.5	84.2
0°-60°	352.9	97.0
0°-90°	364.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	364.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	421	
5°	410	38
15°	334	93
25°	223	102
35°	118	74
45°	44	35
55°	12	11
65°	6	6
75°	4	3
85°	1	1
90°	0	

TEST NUMBER: P1251366

CATALOG NUMBER: P3AS05R609030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	420.7
2.5°	418.2
5°	409.7
7.5°	396.7
10°	379.2
12.5°	358.2
15°	333.6
17.5°	307.1
20°	279.1
22.5°	250.6
25°	222.6
27.5°	194.6
30°	168.1
32.5°	142.6
35°	118.1
37.5°	96.0
40°	76.0
42.5°	58.5
45°	44.0
47.5°	32.0
50°	22.0
52.5°	14.5
55°	11.5
57.5°	10.0
60°	9.0
62.5°	7.5
65°	6.5
67.5°	5.5
70°	4.5
72.5°	4.0
75°	3.5
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)