

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251378

Luminaire Tested: P3AS05R659030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251378
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 246.0 lumens
Efficiency: N/A
Efficacy: 34.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251378
CATALOG NUMBER: P3AS05R659030DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1251378
 CATALOG NUMBER: P3AS05R659030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58022
5°	57319
10°	55131
15°	51646
20°	46461
25°	39462
30°	30866
35°	21978
40°	14398
45°	8900
50°	4503
55°	1606
60°	1403
65°	1401
70°	1282
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8900 cd/sqm



TEST NUMBER: P1251378
 CATALOG NUMBER: P3AS05R659030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.4	9.9
10°-20°	63.3	25.7
20°-30°	74.0	30.1
30°-40°	51.7	21.0
40°-50°	22.8	9.3
50°-60°	5.1	2.1
60°-70°	2.6	1.0
70°-80°	1.6	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.8	65.8
0°-40°	213.5	86.8
0°-60°	241.4	98.1
0°-90°	246.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	246.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	265	
5°	260	24
15°	228	63
25°	163	74
35°	82	52
45°	29	23
55°	4	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1251378
CATALOG NUMBER: P3AS05R659030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	264.6
2.5°	263.6
5°	260.4
7.5°	255.0
10°	247.6
12.5°	238.6
15°	227.5
17.5°	214.1
20°	199.1
22.5°	182.2
25°	163.1
27.5°	142.9
30°	121.9
32.5°	101.5
35°	82.1
37.5°	65.2
40°	50.3
42.5°	38.0
45°	28.7
47.5°	21.1
50°	13.2
52.5°	6.9
55°	4.2
57.5°	3.7
60°	3.2
62.5°	2.9
65°	2.7
67.5°	2.2
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)