

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251393

Luminaire Tested: P3AS05R659030DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251393
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659030DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 347.0 lumens
Efficiency: N/A
Efficacy: 48.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251393
CATALOG NUMBER: P3AS05R659030DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1251393
 CATALOG NUMBER: P3AS05R659030DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	88195
5°	86000
10°	80092
15°	71782
20°	62002
25°	51559
30°	40664
35°	30142
40°	20753
45°	12870
50°	6993
55°	4396
60°	3728
65°	3373
70°	2885
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12870 cd/sqm



TEST NUMBER: P1251393
 CATALOG NUMBER: P3AS05R659030DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.3	10.5
10°-20°	87.9	25.3
20°-30°	97.2	28.0
30°-40°	70.6	20.3
40°-50°	33.0	9.5
50°-60°	11.1	3.2
60°-70°	6.4	1.9
70°-80°	3.4	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	221.3	63.8
0°-40°	291.9	84.1
0°-60°	336.1	96.9
0°-90°	347.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	347.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	402	
5°	391	36
15°	316	88
25°	213	97
35°	113	71
45°	42	33
55°	12	11
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1251393
CATALOG NUMBER: P3AS05R659030DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	402.2
2.5°	399.7
5°	390.7
7.5°	377.2
10°	359.7
12.5°	339.2
15°	316.2
17.5°	291.2
20°	265.7
22.5°	239.1
25°	213.1
27.5°	186.6
30°	160.6
32.5°	135.6
35°	112.6
37.5°	91.6
40°	72.5
42.5°	55.5
45°	41.5
47.5°	30.0
50°	20.5
52.5°	14.0
55°	11.5
57.5°	10.0
60°	8.5
62.5°	7.5
65°	6.5
67.5°	5.5
70°	4.5
72.5°	4.0
75°	3.0
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)