

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251403

Luminaire Tested: P3AS05R709030DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709030DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 596.9 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251403

CATALOG NUMBER: P3AS05R709030DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1251403

CATALOG NUMBER: P3AS05R709030DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		86
4	95	87	82	77	94	86	81	77	84	79	76		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		55	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116087
5°	109465
10°	103783
15°	101930
20°	98242
25°	92618
30°	91938
35°	80067
40°	51811
45°	24499
50°	3446
55°	268
60°	219
65°	259
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24499 cd/sqm

TEST NUMBER: P1251403

CATALOG NUMBER: P3AS05R709030DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.4	7.8
10°-20°	126.1	21.1
20°-30°	178.4	29.9
30°-40°	179.2	30.0
40°-50°	64.5	10.8
50°-60°	1.7	0.3
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	350.9	58.8
0°-40°	530.1	88.8
0°-60°	596.3	99.9
0°-90°	596.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	529	
5°	497	46
15°	449	126
25°	383	178
35°	299	179
45°	79	64
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1251403

CATALOG NUMBER: P3AS05R709030DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	529.4
1°	527.9
2°	523.2
3°	515.9
4°	506.6
5°	497.3
6°	488.4
7°	481.6
8°	475.4
9°	470.5
10°	466.1
11°	462.4
12°	459.0
13°	455.6
14°	452.4
15°	449.0
16°	444.8
17°	440.4
18°	435.0
19°	428.4
20°	421.0
21°	412.9
22°	404.8
23°	397.0
24°	389.4
25°	382.8
26°	378.1
27°	374.4
28°	371.5
29°	368.0
30°	363.1
31°	356.0
32°	346.0
32.5°	340.3
33°	332.7
34°	317.8
35°	299.1
36°	278.5
37°	255.2
37.5°	244.5
38°	229.7
39°	203.5
40°	181.0
42.5°	125.3
45°	79.0

TEST NUMBER: P1251403

CATALOG NUMBER: P3AS05R709030DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	42.4
50°	10.1
52.5°	1.2
55°	0.7
57.5°	0.7
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)