

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251407

Luminaire Tested: P3AS05R709030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251407
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 247.0 lumens
Efficiency: N/A
Efficacy: 34.3 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251407

CATALOG NUMBER: P3AS05R709030DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1251407

CATALOG NUMBER: P3AS05R709030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47825
5°	47237
10°	45869
15°	43928
20°	41164
25°	37381
30°	32309
35°	25752
40°	18749
45°	12311
50°	5765
55°	1797
60°	1710
65°	1660
70°	1603
75°	1694
80°	1515
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12311 cd/sqm

TEST NUMBER: P1251407

CATALOG NUMBER: P3AS05R709030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.2	8.2
10°-20°	54.2	21.9
20°-30°	70.4	28.5
30°-40°	59.8	24.2
40°-50°	30.8	12.5
50°-60°	5.9	2.4
60°-70°	3.2	1.3
70°-80°	2.0	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.8	58.6
0°-40°	204.5	82.8
0°-60°	241.3	97.7
0°-90°	247.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	247.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	218	
5°	215	20
15°	194	54
25°	154	70
35°	96	60
45°	40	31
55°	5	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1251407

CATALOG NUMBER: P3AS05R709030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	218.1
2.5°	217.3
5°	214.6
7.5°	210.7
10°	206.0
12.5°	200.2
15°	193.5
17.5°	185.4
20°	176.4
22.5°	166.1
25°	154.5
27.5°	141.5
30°	127.6
32.5°	112.1
35°	96.2
37.5°	80.5
40°	65.5
42.5°	51.5
45°	39.7
47.5°	29.2
50°	16.9
52.5°	7.4
55°	4.7
57.5°	4.4
60°	3.9
62.5°	3.7
65°	3.2
67.5°	2.9
70°	2.5
72.5°	2.2
75°	2.0
77.5°	1.5
80°	1.2
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)