

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250231

Luminaire Tested: P3AS24R159027D010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R159027D010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1876.0 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250231

CATALOG NUMBER: P3AS24R159027D010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1250231

CATALOG NUMBER: P3AS24R159027D010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1602591
5°	1422536
10°	987891
15°	584226
20°	332739
25°	190196
30°	105257
35°	56108
40°	31030
45°	16808
50°	10473
55°	8296
60°	7149
65°	6590
70°	5770
75°	6100
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16808 cd/sqm

TEST NUMBER: P1250231

CATALOG NUMBER: P3AS24R159027D010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.6	29.3
10°-20°	725.3	38.7
20°-30°	373.4	19.9
30°-40°	140.2	7.5
40°-50°	45.9	2.4
50°-60°	19.7	1.1
60°-70°	12.5	0.7
70°-80°	7.4	0.4
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1648.3	87.9
0°-40°	1788.5	95.3
0°-60°	1854.1	98.8
0°-90°	1876.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1876.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7308	
5°	6463	550
15°	2574	725
25°	786	373
35°	210	140
45°	54	46
55°	22	20
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1250231

CATALOG NUMBER: P3AS24R159027D010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7308.4
1°	7294.0
2°	7198.2
3°	7015.7
4°	6775.3
5°	6462.6
6°	6108.4
7°	5719.9
8°	5287.9
9°	4861.4
10°	4436.7
12.5°	3413.9
15°	2573.5
17.5°	1926.5
20°	1425.9
22.5°	1064.5
25°	786.1
27.5°	572.9
30°	415.7
32.5°	294.6
35°	209.6
37.5°	150.0
40°	108.4
42.5°	77.7
45°	54.2
47.5°	39.8
50°	30.7
52.5°	25.3
55°	21.7
57.5°	18.1
60°	16.3
62.5°	14.5
65°	12.7
67.5°	10.8
70°	9.0
72.5°	9.0
75°	7.2
77.5°	5.4
80°	3.6
82.5°	3.6
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)