

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250232

Luminaire Tested: P3AS24R159027D010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R159027D010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1876.0 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250232
CATALOG NUMBER: P3AS24R159027D010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1250232
 CATALOG NUMBER: P3AS24R159027D010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	87	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	80	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	77	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	74	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	72	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	69	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	67	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1602591
5°	1422536
10°	987891
15°	584226
20°	332739
25°	190196
30°	105257
35°	56108
40°	31030
45°	16808
50°	10473
55°	8296
60°	7149
65°	6590
70°	5770
75°	6100
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16808 cd/sqm



TEST NUMBER: P1250232
 CATALOG NUMBER: P3AS24R159027D010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.6	29.3
10°-20°	725.3	38.7
20°-30°	373.4	19.9
30°-40°	140.2	7.5
40°-50°	45.9	2.4
50°-60°	19.7	1.1
60°-70°	12.5	0.7
70°-80°	7.4	0.4
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1648.3	87.9
0°-40°	1788.5	95.3
0°-60°	1854.1	98.8
0°-90°	1876.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1876.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7308	
5°	6463	550
15°	2574	725
25°	786	373
35°	210	140
45°	54	46
55°	22	20
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1250232
CATALOG NUMBER: P3AS24R159027D010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7308.4
1°	7294.0
2°	7198.2
3°	7015.7
4°	6775.3
5°	6462.6
6°	6108.4
7°	5719.9
8°	5287.9
9°	4861.4
10°	4436.7
12.5°	3413.9
15°	2573.5
17.5°	1926.5
20°	1425.9
22.5°	1064.5
25°	786.1
27.5°	572.9
30°	415.7
32.5°	294.6
35°	209.6
37.5°	150.0
40°	108.4
42.5°	77.7
45°	54.2
47.5°	39.8
50°	30.7
52.5°	25.3
55°	21.7
57.5°	18.1
60°	16.3
62.5°	14.5
65°	12.7
67.5°	10.8
70°	9.0
72.5°	9.0
75°	7.2
77.5°	5.4
80°	3.6
82.5°	3.6
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)