

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250271

Luminaire Tested: P3AS24R209027D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R209027D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1423.0 lumens
Efficiency: N/A
Efficacy: 49.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250271
CATALOG NUMBER: P3AS24R209027D010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1250271
 CATALOG NUMBER: P3AS24R209027D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.0	10.1
10°-20°	340.2	23.9
20°-30°	377.6	26.5
30°-40°	288.0	20.2
40°-50°	147.5	10.4
50°-60°	60.6	4.3
60°-70°	37.8	2.7
70°-80°	21.2	1.5
80°-90°	6.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	861.8	60.6
0°-40°	1149.8	80.8
0°-60°	1357.9	95.4
0°-90°	1423.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1423.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1605	
5°	1556	144
15°	1222	340
25°	826	378
35°	459	288
45°	186	147
55°	62	61
65°	38	38
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P1250271
CATALOG NUMBER: P3AS24R209027D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1605.2
1°	1607.0
2°	1599.7
3°	1590.7
4°	1576.2
5°	1556.4
6°	1532.9
7°	1507.5
8°	1480.4
9°	1447.9
10°	1415.4
12.5°	1321.4
15°	1221.9
17.5°	1120.7
20°	1019.5
22.5°	918.3
25°	826.1
27.5°	733.9
30°	638.1
32.5°	547.7
35°	459.1
37.5°	381.4
40°	305.5
42.5°	240.4
45°	186.2
47.5°	141.0
50°	104.8
52.5°	77.7
55°	61.5
57.5°	56.0
60°	48.8
62.5°	43.4
65°	38.0
67.5°	32.5
70°	28.9
72.5°	23.5
75°	19.9
77.5°	16.3
80°	12.7
82.5°	9.0
85°	5.4
87.5°	1.8
90°	0.0

(END OF REPORT)