

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251526

Luminaire Tested: P3AS09R259030DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259030DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 766.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251526

CATALOG NUMBER: P3AS09R259030DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251526

CATALOG NUMBER: P3AS09R259030DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	491364
5°	458440
10°	367239
15°	249286
20°	150840
25°	88215
30°	50236
35°	27626
40°	14656
45°	7722
50°	4503
55°	3364
60°	2895
65°	3061
70°	2821
75°	2457
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7722 cd/sqm

TEST NUMBER: P1251526

CATALOG NUMBER: P3AS09R259030DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	24.1
10°-20°	301.9	39.4
20°-30°	172.5	22.5
30°-40°	68.1	8.9
40°-50°	20.9	2.7
50°-60°	8.3	1.1
60°-70°	5.5	0.7
70°-80°	3.1	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.2	86.1
0°-40°	727.3	94.9
0°-60°	756.4	98.7
0°-90°	766.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2241	
5°	2083	185
15°	1098	302
25°	365	173
35°	103	68
45°	25	21
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1251526

CATALOG NUMBER: P3AS09R259030DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2240.8
1°	2236.4
2°	2218.1
3°	2185.9
4°	2141.2
5°	2082.7
6°	2013.8
7°	1936.3
8°	1846.2
9°	1754.0
10°	1649.3
11°	1546.1
12°	1432.6
13°	1320.6
14°	1205.7
15°	1098.1
17.5°	851.4
20°	646.4
22.5°	485.3
25°	364.6
27.5°	270.1
30°	198.4
32.5°	143.5
35°	103.2
37.5°	73.2
40°	51.2
42.5°	35.1
45°	24.9
47.5°	17.6
50°	13.2
52.5°	10.2
55°	8.8
57.5°	8.1
60°	6.6
62.5°	5.9
65°	5.9
67.5°	5.1
70°	4.4
72.5°	3.7
75°	2.9
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.7



TEST NUMBER: P1251526
CATALOG NUMBER: P3AS09R259030DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)