

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251575

Luminaire Tested: P3AS09R359030DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359030DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 929.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251575
CATALOG NUMBER: P3AS09R359030DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1251575
 CATALOG NUMBER: P3AS09R359030DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	94	94	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	77	74	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	605763
5°	593439
10°	552072
15°	404747
20°	207265
25°	74690
30°	29093
35°	10172
40°	4179
45°	1147
50°	989
55°	1109
60°	965
65°	778
70°	962
75°	1271
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 1271 cd/sqm



TEST NUMBER: P1251575
 CATALOG NUMBER: P3AS09R359030DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.3	27.1
10°-20°	471.6	50.8
20°-30°	167.0	18.0
30°-40°	29.2	3.1
40°-50°	4.3	0.5
50°-60°	2.4	0.3
60°-70°	1.7	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	889.9	95.8
0°-40°	919.1	98.9
0°-60°	925.7	99.6
0°-90°	929.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	929.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2762	
5°	2696	251
15°	1783	472
25°	309	167
35°	38	29
45°	4	4
55°	3	2
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1251575
CATALOG NUMBER: P3AS09R359030DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2762.5
1°	2761.8
2°	2753.0
3°	2736.2
4°	2720.8
5°	2696.0
6°	2670.3
7°	2641.8
8°	2606.7
9°	2551.8
10°	2479.4
11°	2379.2
12°	2258.5
13°	2115.1
14°	1957.0
15°	1782.9
17.5°	1327.9
20°	888.2
22.5°	535.5
25°	308.7
27.5°	184.4
30°	114.9
32.5°	66.6
35°	38.0
37.5°	24.1
40°	14.6
42.5°	7.3
45°	3.7
47.5°	2.9
50°	2.9
52.5°	2.9
55°	2.9
57.5°	2.2
60°	2.2
62.5°	2.2
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0



TEST NUMBER: P1251575
CATALOG NUMBER: P3AS09R359030DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)