

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251583

Luminaire Tested: P3AS09R359030DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359030DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 769.0 lumens
Efficiency: N/A
Efficacy: 69.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251583

CATALOG NUMBER: P3AS09R359030DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1251583

CATALOG NUMBER: P3AS09R359030DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	387842
5°	372748
10°	324777
15°	248764
20°	166428
25°	100699
30°	57781
35°	32310
40°	17175
45°	8838
50°	4230
55°	3364
60°	3201
65°	2646
70°	2821
75°	2457
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8838 cd/sqm

TEST NUMBER: P1251583

CATALOG NUMBER: P3AS09R359030DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.1	20.0
10°-20°	298.6	38.8
20°-30°	195.5	25.4
30°-40°	79.3	10.3
40°-50°	23.8	3.1
50°-60°	8.1	1.0
60°-70°	5.4	0.7
70°-80°	3.2	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	648.1	84.3
0°-40°	727.4	94.6
0°-60°	759.3	98.7
0°-90°	769.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	769.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1769	
5°	1693	154
15°	1096	299
25°	416	195
35°	121	79
45°	28	24
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1251583

CATALOG NUMBER: P3AS09R359030DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1768.7
1°	1765.8
2°	1757.8
3°	1741.7
4°	1722.7
5°	1693.4
6°	1656.8
7°	1615.9
8°	1569.8
9°	1517.1
10°	1458.6
11°	1393.5
12°	1325.5
13°	1249.4
14°	1177.0
15°	1095.8
17.5°	899.0
20°	713.2
22.5°	548.6
25°	416.2
27.5°	310.2
30°	228.2
32.5°	167.5
35°	120.7
37.5°	85.6
40°	60.0
42.5°	41.7
45°	28.5
47.5°	19.0
50°	12.4
52.5°	9.5
55°	8.8
57.5°	8.0
60°	7.3
62.5°	6.6
65°	5.1
67.5°	4.4
70°	4.4
72.5°	3.7
75°	2.9
77.5°	2.2
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7



TEST NUMBER: P1251583
CATALOG NUMBER: P3AS09R359030DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)