

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251598

Luminaire Tested: P3AS09R359030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 475.1 lumens
Efficiency: N/A
Efficacy: 42.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251598

CATALOG NUMBER: P3AS09R359030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251598

CATALOG NUMBER: P3AS09R359030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152685
5°	148910
10°	136136
15°	115551
20°	91475
25°	69198
30°	50362
35°	34077
40°	20925
45°	12032
50°	7232
55°	5887
60°	5131
65°	4566
70°	3783
75°	3728
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12032 cd/sqm

TEST NUMBER: P1251598

CATALOG NUMBER: P3AS09R359030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.5	13.2
10°-20°	140.3	29.5
20°-30°	131.3	27.6
30°-40°	80.4	16.9
40°-50°	31.7	6.7
50°-60°	14.0	2.9
60°-70°	8.7	1.8
70°-80°	4.6	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.1	70.3
0°-40°	414.5	87.3
0°-60°	460.1	96.9
0°-90°	475.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	475.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	696	
5°	676	63
15°	509	140
25°	286	131
35°	127	80
45°	39	32
55°	15	14
65°	9	9
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1251598

CATALOG NUMBER: P3AS09R359030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	696.3
1°	697.0
2°	694.8
3°	690.4
4°	683.8
5°	676.5
6°	667.0
7°	656.0
8°	642.9
9°	628.2
10°	611.4
11°	593.9
12°	574.9
13°	554.4
14°	531.7
15°	509.0
17.5°	450.5
20°	392.0
22.5°	335.7
25°	286.0
27.5°	239.9
30°	198.9
32.5°	160.9
35°	127.3
37.5°	97.3
40°	73.1
42.5°	52.7
45°	38.8
47.5°	27.8
50°	21.2
52.5°	17.6
55°	15.4
57.5°	13.2
60°	11.7
62.5°	10.2
65°	8.8
67.5°	7.3
70°	5.9
72.5°	5.1
75°	4.4
77.5°	3.7
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7



TEST NUMBER: P1251598

CATALOG NUMBER: P3AS09R359030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)