

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250324

Luminaire Tested: P3AS24R309027D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R309027D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1914.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250324

CATALOG NUMBER: P3AS24R309027D010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250324

CATALOG NUMBER: P3AS24R309027D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1116884
5°	1063039
10°	894172
15°	644839
20°	399991
25°	227481
30°	126349
35°	68717
40°	36239
45°	19630
50°	10473
55°	6920
60°	6359
65°	6590
70°	5770
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19630 cd/sqm

TEST NUMBER: P1250324

CATALOG NUMBER: P3AS24R309027D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.9	22.7
10°-20°	773.0	40.4
20°-30°	446.8	23.3
30°-40°	169.5	8.9
40°-50°	52.0	2.7
50°-60°	17.5	0.9
60°-70°	11.9	0.6
70°-80°	6.4	0.3
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1654.6	86.4
0°-40°	1824.2	95.3
0°-60°	1893.8	98.9
0°-90°	1914.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1914.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5093	
5°	4829	435
15°	2840	773
25°	940	447
35°	257	170
45°	63	52
55°	18	18
65°	13	12
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1250324

CATALOG NUMBER: P3AS24R309027D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5093.4
1°	5089.8
2°	5059.0
3°	5001.2
4°	4928.8
5°	4829.4
6°	4702.8
7°	4561.8
8°	4404.5
9°	4216.5
10°	4015.8
11°	3798.8
12°	3569.2
13°	3328.7
14°	3084.6
15°	2840.5
17.5°	2240.2
20°	1714.1
22.5°	1271.1
25°	940.2
27.5°	683.5
30°	499.0
32.5°	359.8
35°	256.7
37.5°	179.0
40°	126.6
42.5°	88.6
45°	63.3
47.5°	43.4
50°	30.7
52.5°	21.7
55°	18.1
57.5°	16.3
60°	14.5
62.5°	12.7
65°	12.7
67.5°	10.8
70°	9.0
72.5°	7.2
75°	5.4
77.5°	5.4
80°	3.6
82.5°	3.6
85°	1.8
87.5°	0.0



TEST NUMBER: P1250324

CATALOG NUMBER: P3AS24R309027D010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)