

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251645

Luminaire Tested: P3AS09R459030DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459030DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 635.0 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251645

CATALOG NUMBER: P3AS09R459030DE010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1251645

CATALOG NUMBER: P3AS09R459030DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75		
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69		
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50		
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47		
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134638
5°	132247
10°	125137
15°	114121
20°	100925
25°	87634
30°	75227
35°	62694
40°	46716
45°	28592
50°	13236
55°	10360
60°	9955
65°	9132
70°	8463
75°	8049
80°	7450
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28592 cd/sqm

TEST NUMBER: P1251645

CATALOG NUMBER: P3AS09R459030DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	8.8
10°-20°	140.0	22.0
20°-30°	166.3	26.2
30°-40°	144.5	22.8
40°-50°	72.5	11.4
50°-60°	25.2	4.0
60°-70°	17.7	2.8
70°-80°	9.8	1.6
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.4	57.1
0°-40°	506.9	79.8
0°-60°	604.5	95.2
0°-90°	635.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	635.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	614	
5°	601	56
15°	503	140
25°	362	166
35°	234	145
45°	92	72
55°	27	25
65°	18	18
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1251645

CATALOG NUMBER: P3AS09R459030DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	614.0
2.5°	611.1
5°	600.8
7.5°	584.7
10°	562.0
12.5°	534.2
15°	502.7
17.5°	467.6
20°	432.5
22.5°	396.6
25°	362.2
27.5°	329.3
30°	297.1
32.5°	266.4
35°	234.2
37.5°	199.8
40°	163.2
42.5°	127.3
45°	92.2
47.5°	60.7
50°	38.8
52.5°	30.0
55°	27.1
57.5°	24.9
60°	22.7
62.5°	20.5
65°	17.6
67.5°	15.4
70°	13.2
72.5°	11.0
75°	9.5
77.5°	7.3
80°	5.9
82.5°	4.4
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)