

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251684

Luminaire Tested: P3AS09R509030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 540.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251684

CATALOG NUMBER: P3AS09R509030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251684

CATALOG NUMBER: P3AS09R509030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		73
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		53
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157049
5°	152828
10°	140924
15°	123928
20°	103702
25°	82214
30°	60338
35°	41466
40°	26364
45°	14730
50°	7983
55°	6690
60°	5789
65°	5292
70°	4680
75°	4321
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14730 cd/sqm

TEST NUMBER: P1251684

CATALOG NUMBER: P3AS09R509030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	11.9
10°-20°	151.2	28.0
20°-30°	154.7	28.6
30°-40°	98.1	18.2
40°-50°	39.0	7.2
50°-60°	15.8	2.9
60°-70°	10.1	1.9
70°-80°	5.2	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.2	68.6
0°-40°	468.2	86.7
0°-60°	523.1	96.9
0°-90°	540.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	540.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	716	
5°	694	64
15°	546	151
25°	340	155
35°	155	98
45°	48	39
55°	18	16
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1251684

CATALOG NUMBER: P3AS09R509030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	716.2
2.5°	711.1
5°	694.3
7.5°	668.0
10°	632.9
12.5°	591.3
15°	545.9
17.5°	496.3
20°	444.4
22.5°	392.5
25°	339.8
27.5°	287.2
30°	238.3
32.5°	194.4
35°	154.9
37.5°	121.3
40°	92.1
42.5°	68.0
45°	47.5
47.5°	32.2
50°	23.4
52.5°	19.7
55°	17.5
57.5°	15.3
60°	13.2
62.5°	11.7
65°	10.2
67.5°	8.8
70°	7.3
72.5°	5.8
75°	5.1
77.5°	3.7
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)