

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250348

Luminaire Tested: P3AS24R359027D010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1250348  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R359027D010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1900.0 lumens  
Efficiency: N/A  
Efficacy: 66.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1250348  
CATALOG NUMBER: P3AS24R359027D010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1250348  
 CATALOG NUMBER: P3AS24R359027D010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	958278
5°	920953
10°	802434
15°	614623
20°	411192
25°	248821
30°	142781
35°	79826
40°	42422
45°	21863
50°	10473
55°	8296
60°	7938
65°	6590
70°	6924
75°	6100
80°	6819
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21863 cd/sqm



TEST NUMBER: P1250348  
 CATALOG NUMBER: P3AS24R359027D010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	380.7	20.0
10°-20°	737.7	38.8
20°-30°	483.0	25.4
30°-40°	195.9	10.3
40°-50°	58.8	3.1
50°-60°	20.0	1.1
60°-70°	13.4	0.7
70°-80°	7.8	0.4
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1601.4	84.3
0°-40°	1797.3	94.6
0°-60°	1876.1	98.7
0°-90°	1900.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1900.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4370	
5°	4184	381
15°	2707	738
25°	1028	483
35°	298	196
45°	70	59
55°	22	20
65°	13	13
75°	7	8
85°	2	3
90°	0	

TEST NUMBER: P1250348

CATALOG NUMBER: P3AS24R359027D010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4370.1
1°	4362.9
2°	4343.0
3°	4303.2
4°	4256.2
5°	4183.9
6°	4093.6
7°	3992.4
8°	3878.5
9°	3748.4
10°	3603.8
11°	3442.9
12°	3274.9
13°	3086.9
14°	2908.0
15°	2707.4
17.5°	2221.2
20°	1762.1
22.5°	1355.5
25°	1028.4
27.5°	766.3
30°	563.9
32.5°	413.9
35°	298.2
37.5°	211.5
40°	148.2
42.5°	103.0
45°	70.5
47.5°	47.0
50°	30.7
52.5°	23.5
55°	21.7
57.5°	19.9
60°	18.1
62.5°	16.3
65°	12.7
67.5°	10.8
70°	10.8
72.5°	9.0
75°	7.2
77.5°	5.4
80°	5.4
82.5°	3.6
85°	1.8
87.5°	1.8



TEST NUMBER: P1250348  
CATALOG NUMBER: P3AS24R359027D010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)