

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251701

Luminaire Tested: P3AS09R559030DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559030DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 797.0 lumens
Efficiency: N/A
Efficacy: 71.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251701

CATALOG NUMBER: P3AS09R559030DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251701

CATALOG NUMBER: P3AS09R559030DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	218842
5°	216618
10°	209192
15°	193372
20°	166871
25°	131790
30°	93483
35°	60284
40°	36211
45°	20405
50°	10985
55°	3900
60°	3508
65°	3424
70°	3270
75°	3135
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20405 cd/sqm

TEST NUMBER: P1251701

CATALOG NUMBER: P3AS09R559030DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	11.6
10°-20°	235.5	29.6
20°-30°	246.8	31.0
30°-40°	144.0	18.1
40°-50°	53.9	6.8
50°-60°	12.7	1.6
60°-70°	6.5	0.8
70°-80°	3.9	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.9	72.1
0°-40°	719.0	90.2
0°-60°	785.5	98.6
0°-90°	797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	998	
5°	984	93
15°	852	236
25°	545	247
35°	225	144
45°	66	54
55°	10	13
65°	7	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1251701

CATALOG NUMBER: P3AS09R559030DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	998.0
2.5°	995.1
5°	984.1
7.5°	966.6
10°	939.5
12.5°	901.5
15°	851.8
17.5°	788.9
20°	715.1
22.5°	632.5
25°	544.7
27.5°	454.8
30°	369.2
32.5°	291.7
35°	225.2
37.5°	171.1
40°	126.5
42.5°	90.7
45°	65.8
47.5°	47.5
50°	32.2
52.5°	18.3
55°	10.2
57.5°	8.8
60°	8.0
62.5°	7.3
65°	6.6
67.5°	5.8
70°	5.1
72.5°	4.4
75°	3.7
77.5°	2.9
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)