

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251706

Luminaire Tested: P3AS09R559030DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559030DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 619.0 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251706
CATALOG NUMBER: P3AS09R559030DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1251706
 CATALOG NUMBER: P3AS09R559030DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116394
5°	114902
10°	110374
15°	103224
20°	94182
25°	84029
30°	73480
35°	61061
40°	48147
45°	32655
50°	19957
55°	10360
60°	9604
65°	9080
70°	8463
75°	7456
80°	7324
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 32655 cd/sqm



TEST NUMBER: P1251706
 CATALOG NUMBER: P3AS09R559030DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	7.9
10°-20°	127.1	20.5
20°-30°	159.2	25.7
30°-40°	142.1	23.0
40°-50°	83.2	13.4
50°-60°	28.7	4.6
60°-70°	17.4	2.8
70°-80°	9.7	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.2	54.2
0°-40°	477.3	77.1
0°-60°	589.2	95.2
0°-90°	619.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	619.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	531	
5°	522	49
15°	455	127
25°	347	159
35°	228	142
45°	105	83
55°	27	29
65°	18	17
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P1251706
CATALOG NUMBER: P3AS09R559030DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	530.8
2.5°	527.8
5°	522.0
7.5°	510.3
10°	495.7
12.5°	477.4
15°	454.7
17.5°	430.6
20°	403.6
22.5°	375.8
25°	347.3
27.5°	318.8
30°	290.2
32.5°	259.5
35°	228.1
37.5°	197.4
40°	168.2
42.5°	136.7
45°	105.3
47.5°	80.4
50°	58.5
52.5°	38.0
55°	27.1
57.5°	24.1
60°	21.9
62.5°	19.7
65°	17.5
67.5°	15.4
70°	13.2
72.5°	11.0
75°	8.8
77.5°	7.3
80°	5.8
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)