

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251710

Luminaire Tested: P3AS09R559030DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251710
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559030DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 532.0 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251710

CATALOG NUMBER: P3AS09R559030DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1251710

CATALOG NUMBER: P3AS09R559030DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144725
5°	141096
10°	131171
15°	116800
20°	99269
25°	80109
30°	61073
35°	43446
40°	28654
45°	16994
50°	9961
55°	6155
60°	5438
65°	4929
70°	4231
75°	3728
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16994 cd/sqm

TEST NUMBER: P1251710

CATALOG NUMBER: P3AS09R559030DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	11.2
10°-20°	142.6	26.8
20°-30°	151.1	28.4
30°-40°	102.1	19.2
40°-50°	44.7	8.4
50°-60°	16.0	3.0
60°-70°	9.4	1.8
70°-80°	4.9	0.9
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.2	66.4
0°-40°	455.3	85.6
0°-60°	516.1	97.0
0°-90°	532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	641	60
15°	514	143
25°	331	151
35°	162	102
45°	55	45
55°	16	16
65°	10	9
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1251710

CATALOG NUMBER: P3AS09R559030DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	660.0
2.5°	654.9
5°	641.0
7.5°	618.3
10°	589.1
12.5°	554.0
15°	514.5
17.5°	470.7
20°	425.4
22.5°	377.9
25°	331.1
27.5°	285.0
30°	241.2
32.5°	199.5
35°	162.3
37.5°	128.6
40°	100.1
42.5°	75.3
45°	54.8
47.5°	40.2
50°	29.2
52.5°	20.5
55°	16.1
57.5°	14.6
60°	12.4
62.5°	11.0
65°	9.5
67.5°	8.0
70°	6.6
72.5°	5.8
75°	4.4
77.5°	3.7
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)