

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250387

Luminaire Tested: P3AS24R409027D010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1250387  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R409027D010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1615.0 lumens  
Efficiency: N/A  
Efficacy: 56.1 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1250387  
CATALOG NUMBER: P3AS24R409027D010 E3DLD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1250387  
 CATALOG NUMBER: P3AS24R409027D010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	362537
5°	355953
10°	335532
15°	304769
20°	267750
25°	228642
30°	189396
35°	146080
40°	103966
45°	70054
50°	38208
55°	26952
60°	25349
65°	23453
70°	20837
75°	19910
80°	15911
85°	13586

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 70054 cd/sqm



TEST NUMBER: P1250387  
 CATALOG NUMBER: P3AS24R409027D010 E3DLD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	150.8	9.3
10°-20°	374.0	23.2
20°-30°	432.3	26.8
30°-40°	340.7	21.1
40°-50°	174.9	10.8
50°-60°	66.9	4.1
60°-70°	44.2	2.7
70°-80°	24.1	1.5
80°-90°	7.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	957.1	59.3
0°-40°	1297.8	80.4
0°-60°	1539.6	95.3
0°-90°	1615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1615.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1653	
5°	1617	151
15°	1342	374
25°	945	432
35°	546	341
45°	226	175
55°	70	67
65°	45	44
75°	24	24
85°	5	7
90°	0	

TEST NUMBER: P1250387  
CATALOG NUMBER: P3AS24R409027D010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1653.3
2.5°	1644.3
5°	1617.1
7.5°	1570.2
10°	1506.9
12.5°	1432.8
15°	1342.5
17.5°	1248.5
20°	1147.4
22.5°	1044.4
25°	945.0
27.5°	845.6
30°	748.0
32.5°	648.7
35°	545.7
37.5°	449.9
40°	363.2
42.5°	289.1
45°	225.9
47.5°	164.4
50°	112.0
52.5°	81.3
55°	70.5
57.5°	63.2
60°	57.8
62.5°	50.6
65°	45.2
67.5°	37.9
70°	32.5
72.5°	27.1
75°	23.5
77.5°	18.1
80°	12.6
82.5°	10.8
85°	5.4
87.5°	3.6
90°	0.0

(END OF REPORT)