

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251711

Luminaire Tested: P3AS09R559030DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1251711  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R559030DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 532.0 lumens  
Efficiency: N/A  
Efficacy: 47.9 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1251711  
CATALOG NUMBER: P3AS09R559030DE010 E3DLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1251711  
 CATALOG NUMBER: P3AS09R559030DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	144725
5°	141096
10°	131171
15°	116800
20°	99269
25°	80109
30°	61073
35°	43446
40°	28654
45°	16994
50°	9961
55°	6155
60°	5438
65°	4929
70°	4231
75°	3728
80°	3662
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16994 cd/sqm



TEST NUMBER: P1251711  
 CATALOG NUMBER: P3AS09R559030DE010 E3DLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.5	11.2
10°-20°	142.6	26.8
20°-30°	151.1	28.4
30°-40°	102.1	19.2
40°-50°	44.7	8.4
50°-60°	16.0	3.0
60°-70°	9.4	1.8
70°-80°	4.9	0.9
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.2	66.4
0°-40°	455.3	85.6
0°-60°	516.1	97.0
0°-90°	532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	660	
5°	641	60
15°	514	143
25°	331	151
35°	162	102
45°	55	45
55°	16	16
65°	10	9
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P1251711  
CATALOG NUMBER: P3AS09R559030DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	660.0
2.5°	654.9
5°	641.0
7.5°	618.3
10°	589.1
12.5°	554.0
15°	514.5
17.5°	470.7
20°	425.4
22.5°	377.9
25°	331.1
27.5°	285.0
30°	241.2
32.5°	199.5
35°	162.3
37.5°	128.6
40°	100.1
42.5°	75.3
45°	54.8
47.5°	40.2
50°	29.2
52.5°	20.5
55°	16.1
57.5°	14.6
60°	12.4
62.5°	11.0
65°	9.5
67.5°	8.0
70°	6.6
72.5°	5.8
75°	4.4
77.5°	3.7
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)