

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250405

Luminaire Tested: P3AS24R459027D010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250405
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R459027D010 E3DL1H
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2021.0 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250405

CATALOG NUMBER: P3AS24R459027D010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1250405

CATALOG NUMBER: P3AS24R459027D010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	758952
5°	741160
10°	681328
15°	577302
20°	447899
25°	313107
30°	197246
35°	116125
40°	65695
45°	31941
50°	11087
55°	8984
60°	8727
65°	8457
70°	8142
75°	7625
80°	6819
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31941 cd/sqm

TEST NUMBER: P1250405

CATALOG NUMBER: P3AS24R459027D010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.7	15.4
10°-20°	698.3	34.6
20°-30°	593.0	29.3
30°-40°	282.9	14.0
40°-50°	85.2	4.2
50°-60°	21.6	1.1
60°-70°	16.1	0.8
70°-80°	9.5	0.5
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1603.0	79.3
0°-40°	1885.9	93.3
0°-60°	1992.6	98.6
0°-90°	2021.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2021.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3461	
5°	3367	312
15°	2543	698
25°	1294	593
35°	434	283
45°	103	85
55°	24	22
65°	16	16
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1250405

CATALOG NUMBER: P3AS24R459027D010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3461.1
2.5°	3439.4
5°	3367.1
7.5°	3242.4
10°	3059.9
12.5°	2817.7
15°	2543.0
17.5°	2237.5
20°	1919.4
22.5°	1595.9
25°	1294.1
27.5°	1019.4
30°	779.0
32.5°	585.6
35°	433.8
37.5°	319.9
40°	229.5
42.5°	159.0
45°	103.0
47.5°	57.8
50°	32.5
52.5°	25.3
55°	23.5
57.5°	21.7
60°	19.9
62.5°	18.1
65°	16.3
67.5°	14.5
70°	12.7
72.5°	10.8
75°	9.0
77.5°	7.2
80°	5.4
82.5°	3.6
85°	1.8
87.5°	1.8
90°	0.0

(END OF REPORT)