

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250421

Luminaire Tested: P3AS24R459027D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R459027D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1304.0 lumens
Efficiency: N/A
Efficacy: 45.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250421
CATALOG NUMBER: P3AS24R459027D010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1250421
 CATALOG NUMBER: P3AS24R459027D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	388412
5°	379550
10°	350138
15°	304451
20°	250108
25°	194600
30°	143693
35°	101134
40°	63118
45°	34205
50°	18490
55°	15904
60°	14253
65°	12193
70°	10450
75°	10760
80°	9092
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34205 cd/sqm



TEST NUMBER: P1250421
 CATALOG NUMBER: P3AS24R459027D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	12.2
10°-20°	370.8	28.4
20°-30°	368.1	28.2
30°-40°	237.0	18.2
40°-50°	91.3	7.0
50°-60°	37.1	2.8
60°-70°	23.5	1.8
70°-80°	12.6	1.0
80°-90°	3.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	898.5	68.9
0°-40°	1135.5	87.1
0°-60°	1264.0	96.9
0°-90°	1304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1304.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1771	
5°	1724	160
15°	1341	371
25°	804	368
35°	378	237
45°	110	91
55°	42	37
65°	24	23
75°	13	13
85°	4	4
90°	0	

TEST NUMBER: P1250421
CATALOG NUMBER: P3AS24R459027D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1771.3
2.5°	1762.3
5°	1724.3
7.5°	1659.2
10°	1572.5
12.5°	1464.0
15°	1341.1
17.5°	1207.4
20°	1071.8
22.5°	934.4
25°	804.3
27.5°	681.4
30°	567.5
32.5°	468.1
35°	377.8
37.5°	296.4
40°	220.5
42.5°	159.1
45°	110.3
47.5°	74.1
50°	54.2
52.5°	45.2
55°	41.6
57.5°	36.1
60°	32.5
62.5°	27.1
65°	23.5
67.5°	19.9
70°	16.3
72.5°	14.5
75°	12.7
77.5°	9.0
80°	7.2
82.5°	5.4
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)