

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251741

Luminaire Tested: P3AS09R609030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 770.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251741

CATALOG NUMBER: P3AS09R609030DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1251741

CATALOG NUMBER: P3AS09R609030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181828
5°	180101
10°	174858
15°	163815
20°	144983
25°	121289
30°	95053
35°	68958
40°	45886
45°	28592
50°	15488
55°	4473
60°	4166
65°	3788
70°	3783
75°	3728
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28592 cd/sqm

TEST NUMBER: P1251741

CATALOG NUMBER: P3AS09R609030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.0	10.0
10°-20°	200.2	26.0
20°-30°	228.2	29.6
30°-40°	161.8	21.0
40°-50°	73.4	9.5
50°-60°	15.6	2.0
60°-70°	7.5	1.0
70°-80°	4.6	0.6
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	505.4	65.6
0°-40°	667.3	86.7
0°-60°	756.3	98.2
0°-90°	770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	829	
5°	818	77
15°	722	200
25°	501	228
35°	258	162
45°	92	73
55°	12	16
65°	7	8
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1251741

CATALOG NUMBER: P3AS09R609030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	829.2
2.5°	826.2
5°	818.2
7.5°	804.3
10°	785.3
12.5°	758.2
15°	721.6
17.5°	675.5
20°	621.3
22.5°	562.8
25°	501.3
27.5°	438.4
30°	375.4
32.5°	315.4
35°	257.6
37.5°	206.4
40°	160.3
42.5°	121.5
45°	92.2
47.5°	68.8
50°	45.4
52.5°	21.2
55°	11.7
57.5°	10.2
60°	9.5
62.5°	8.8
65°	7.3
67.5°	6.6
70°	5.9
72.5°	5.1
75°	4.4
77.5°	3.7
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)