

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251742

Luminaire Tested: P3AS09R609030DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1251742  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R609030DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 532.0 lumens  
Efficiency: N/A  
Efficacy: 47.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1251742  
CATALOG NUMBER: P3AS09R609030DE010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1251742  
 CATALOG NUMBER: P3AS09R609030DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134836
5°	131807
10°	123400
15°	110693
20°	95208
25°	78706
30°	62187
35°	46177
40°	31802
45°	19940
50°	10985
55°	6423
60°	5789
65°	4929
70°	4231
75°	4321
80°	3662
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19940 cd/sqm



TEST NUMBER: P1251742  
 CATALOG NUMBER: P3AS09R609030DE010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.7	10.5
10°-20°	135.4	25.5
20°-30°	148.5	27.9
30°-40°	108.2	20.3
40°-50°	51.1	9.6
50°-60°	16.7	3.1
60°-70°	9.5	1.8
70°-80°	5.1	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	339.7	63.9
0°-40°	448.0	84.2
0°-60°	515.8	97.0
0°-90°	532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	615	
5°	599	56
15°	488	135
25°	325	149
35°	172	108
45°	64	51
55°	17	17
65°	10	9
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1251742

CATALOG NUMBER: P3AS09R609030DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	614.9
2.5°	611.2
5°	598.8
7.5°	579.8
10°	554.2
12.5°	523.5
15°	487.6
17.5°	448.9
20°	408.0
22.5°	366.3
25°	325.3
27.5°	284.4
30°	245.6
32.5°	208.4
35°	172.5
37.5°	140.4
40°	111.1
42.5°	85.5
45°	64.3
47.5°	46.8
50°	32.2
52.5°	21.2
55°	16.8
57.5°	14.6
60°	13.2
62.5°	11.0
65°	9.5
67.5°	8.0
70°	6.6
72.5°	5.8
75°	5.1
77.5°	3.7
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)