

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250433

Luminaire Tested: P3AS24R509027D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R509027D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 997.0 lumens
Efficiency: N/A
Efficacy: 34.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250433

CATALOG NUMBER: P3AS24R509027D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1250433

CATALOG NUMBER: P3AS24R509027D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	317431
5°	311027
10°	291333
15°	260796
20°	219469
25°	167502
30°	108852
35°	64541
40°	37298
45°	18700
50°	6959
55°	5429
60°	5043
65°	4618
70°	4552
75°	4490
80°	4420
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18700 cd/sqm

TEST NUMBER: P1250433

CATALOG NUMBER: P3AS24R509027D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.5	13.2
10°-20°	317.7	31.9
20°-30°	311.7	31.3
30°-40°	157.0	15.8
40°-50°	49.6	5.0
50°-60°	12.9	1.3
60°-70°	9.1	0.9
70°-80°	5.6	0.6
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	760.8	76.3
0°-40°	917.9	92.1
0°-60°	980.4	98.3
0°-90°	997.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	997.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1448	
5°	1413	131
15°	1149	318
25°	692	312
35°	241	157
45°	60	50
55°	14	13
65°	9	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1250433

CATALOG NUMBER: P3AS24R509027D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1447.6
2.5°	1438.7
5°	1413.0
7.5°	1366.9
10°	1308.4
12.5°	1233.1
15°	1148.8
17.5°	1051.3
20°	940.5
22.5°	820.9
25°	692.3
27.5°	555.8
30°	429.9
32.5°	323.6
35°	241.1
37.5°	178.2
40°	130.3
42.5°	92.2
45°	60.3
47.5°	34.6
50°	20.4
52.5°	15.1
55°	14.2
57.5°	12.4
60°	11.5
62.5°	10.6
65°	8.9
67.5°	8.0
70°	7.1
72.5°	6.2
75°	5.3
77.5°	4.4
80°	3.5
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)