

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251819

Luminaire Tested: P3AS10R129030DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1251819  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS10R129030DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 542.0 lumens  
Efficiency: N/A  
Efficacy: 46.3 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1251819  
CATALOG NUMBER: P3AS10R129030DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1251819  
 CATALOG NUMBER: P3AS10R129030DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	136722
5°	132995
10°	121552
15°	106471
20°	91335
25°	76262
30°	61022
35°	45775
40°	33205
45°	21708
50°	13577
55°	9175
60°	8113
65°	7472
70°	7052
75°	6439
80°	6061
85°	5284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21708 cd/sqm



TEST NUMBER: P1251819  
 CATALOG NUMBER: P3AS10R129030DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.8	10.3
10°-20°	130.7	24.1
20°-30°	144.0	26.6
30°-40°	107.8	19.9
40°-50°	55.9	10.3
50°-60°	23.1	4.3
60°-70°	14.4	2.6
70°-80°	8.1	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	330.4	61.0
0°-40°	438.2	80.9
0°-60°	517.2	95.4
0°-90°	542.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	542.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	624	
5°	604	56
15°	469	131
25°	315	144
35°	171	108
45°	70	56
55°	24	23
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1251819  
CATALOG NUMBER: P3AS10R129030DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	623.5
1°	624.1
2°	622.1
3°	618.0
4°	611.8
5°	604.2
6°	594.6
7°	584.3
8°	572.0
9°	558.9
10°	545.9
12.5°	508.1
15°	469.0
17.5°	429.8
20°	391.4
22.5°	352.2
25°	315.2
27.5°	278.1
30°	241.0
32.5°	204.6
35°	171.0
37.5°	142.1
40°	116.0
42.5°	92.0
45°	70.0
47.5°	52.9
50°	39.8
52.5°	29.5
55°	24.0
57.5°	21.3
60°	18.5
62.5°	16.5
65°	14.4
67.5°	12.4
70°	11.0
72.5°	8.9
75°	7.6
77.5°	6.2
80°	4.8
82.5°	3.4
85°	2.1
87.5°	0.7
90°	0.0

(END OF REPORT)