

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251872

Luminaire Tested: P3AS13R159030DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159030DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1009.0 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251872

CATALOG NUMBER: P3AS13R159030DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1251872

CATALOG NUMBER: P3AS13R159030DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	861948
5°	765109
10°	531342
15°	314213
20°	178959
25°	102296
30°	56616
35°	30196
40°	16688
45°	9055
50°	5629
55°	4473
60°	3815
65°	3528
70°	3142
75°	3304
80°	2399
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9055 cd/sqm

TEST NUMBER: P1251872

CATALOG NUMBER: P3AS13R159030DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	29.3
10°-20°	390.1	38.7
20°-30°	200.8	19.9
30°-40°	75.4	7.5
40°-50°	24.7	2.4
50°-60°	10.6	1.1
60°-70°	6.7	0.7
70°-80°	4.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	886.5	87.9
0°-40°	961.9	95.3
0°-60°	997.2	98.8
0°-90°	1009.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3931	
5°	3476	296
15°	1384	390
25°	423	201
35°	113	75
45°	29	25
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1251872

CATALOG NUMBER: P3AS13R159030DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3930.8
1°	3923.0
2°	3871.5
3°	3773.3
4°	3644.1
5°	3475.9
6°	3285.4
7°	3076.4
8°	2844.1
9°	2614.7
10°	2386.3
12.5°	1836.1
15°	1384.1
17.5°	1036.2
20°	766.9
22.5°	572.5
25°	422.8
27.5°	308.1
30°	223.6
32.5°	158.4
35°	112.8
37.5°	80.7
40°	58.3
42.5°	41.8
45°	29.2
47.5°	21.4
50°	16.5
52.5°	13.6
55°	11.7
57.5°	9.7
60°	8.7
62.5°	7.8
65°	6.8
67.5°	5.8
70°	4.9
72.5°	4.9
75°	3.9
77.5°	2.9
80°	1.9
82.5°	1.9
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)