

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251875

Luminaire Tested: P3AS13R159030DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1251875  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R159030DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1009.0 lumens  
Efficiency: N/A  
Efficacy: 69.1 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1251875  
CATALOG NUMBER: P3AS13R159030DE010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1251875  
 CATALOG NUMBER: P3AS13R159030DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	93	93	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	88	88	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	85	85	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	81	81	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	78	78	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	75	75	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	73	73	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	70	70	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	68	68	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	861948
5°	765109
10°	531342
15°	314213
20°	178959
25°	102296
30°	56616
35°	30196
40°	16688
45°	9055
50°	5629
55°	4473
60°	3815
65°	3528
70°	3142
75°	3304
80°	2399
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9055 cd/sqm



TEST NUMBER: P1251875  
 CATALOG NUMBER: P3AS13R159030DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	295.6	29.3
10°-20°	390.1	38.7
20°-30°	200.8	19.9
30°-40°	75.4	7.5
40°-50°	24.7	2.4
50°-60°	10.6	1.1
60°-70°	6.7	0.7
70°-80°	4.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	886.5	87.9
0°-40°	961.9	95.3
0°-60°	997.2	98.8
0°-90°	1009.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3931	
5°	3476	296
15°	1384	390
25°	423	201
35°	113	75
45°	29	25
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1251875  
CATALOG NUMBER: P3AS13R159030DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3930.8
1°	3923.0
2°	3871.5
3°	3773.3
4°	3644.1
5°	3475.9
6°	3285.4
7°	3076.4
8°	2844.1
9°	2614.7
10°	2386.3
12.5°	1836.1
15°	1384.1
17.5°	1036.2
20°	766.9
22.5°	572.5
25°	422.8
27.5°	308.1
30°	223.6
32.5°	158.4
35°	112.8
37.5°	80.7
40°	58.3
42.5°	41.8
45°	29.2
47.5°	21.4
50°	16.5
52.5°	13.6
55°	11.7
57.5°	9.7
60°	8.7
62.5°	7.8
65°	6.8
67.5°	5.8
70°	4.9
72.5°	4.9
75°	3.9
77.5°	2.9
80°	1.9
82.5°	1.9
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)