

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250554

Luminaire Tested: P3AS24R709027D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R709027D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1820.0 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250554

CATALOG NUMBER: P3AS24R709027D010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250554

CATALOG NUMBER: P3AS24R709027D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	352340
5°	348117
10°	338048
15°	323725
20°	303243
25°	275508
30°	237961
35°	189660
40°	138145
45°	90800
50°	42540
55°	13113
60°	12674
65°	12193
70°	11605
75°	12285
80°	11365
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 90800 cd/sqm

TEST NUMBER: P1250554

CATALOG NUMBER: P3AS24R709027D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.9	8.2
10°-20°	399.1	21.9
20°-30°	518.7	28.5
30°-40°	440.1	24.2
40°-50°	227.0	12.5
50°-60°	43.7	2.4
60°-70°	23.7	1.3
70°-80°	14.5	0.8
80°-90°	4.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1066.7	58.6
0°-40°	1506.9	82.8
0°-60°	1777.6	97.7
0°-90°	1820.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1820.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1607	
5°	1582	149
15°	1426	399
25°	1139	519
35°	708	440
45°	293	227
55°	34	44
65°	24	24
75°	14	15
85°	4	4
90°	0	

TEST NUMBER: P1250554

CATALOG NUMBER: P3AS24R709027D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1606.8
2.5°	1601.4
5°	1581.5
7.5°	1552.6
10°	1518.2
12.5°	1474.8
15°	1426.0
17.5°	1366.4
20°	1299.5
22.5°	1223.6
25°	1138.7
27.5°	1042.9
30°	939.8
32.5°	826.0
35°	708.5
37.5°	592.8
40°	482.6
42.5°	379.6
45°	292.8
47.5°	215.1
50°	124.7
52.5°	54.2
55°	34.3
57.5°	32.5
60°	28.9
62.5°	27.1
65°	23.5
67.5°	21.7
70°	18.1
72.5°	16.3
75°	14.5
77.5°	10.8
80°	9.0
82.5°	5.4
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)