

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250667

Luminaire Tested: P3AS02R129030DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129030DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 184.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250667

CATALOG NUMBER: P3AS02R129030DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1250667

CATALOG NUMBER: P3AS02R129030DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	71	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	47	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53548
5°	50187
10°	41170
15°	31987
20°	25249
25°	20106
30°	16154
35°	13170
40°	10849
45°	9148
50°	7846
55°	6805
60°	6008
65°	5241
70°	4680
75°	3728
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9148 cd/sqm

TEST NUMBER: P1250667

CATALOG NUMBER: P3AS02R129030DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.4	11.1
10°-20°	39.5	21.4
20°-30°	38.3	20.8
30°-40°	31.0	16.8
40°-50°	23.0	12.5
50°-60°	16.1	8.7
60°-70°	10.1	5.5
70°-80°	4.8	2.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.2	53.4
0°-40°	129.2	70.2
0°-60°	168.2	91.4
0°-90°	184.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	184.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	244	
5°	228	20
15°	141	39
25°	83	38
35°	49	31
45°	30	23
55°	18	16
65°	10	10
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1250667

CATALOG NUMBER: P3AS02R129030DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	244.2
2.5°	240.1
5°	228.0
7.5°	208.7
10°	184.9
12.5°	161.4
15°	140.9
17.5°	123.5
20°	108.2
22.5°	94.8
25°	83.1
27.5°	72.6
30°	63.8
32.5°	56.1
35°	49.2
37.5°	43.2
40°	37.9
42.5°	33.5
45°	29.5
47.5°	26.2
50°	23.0
52.5°	20.2
55°	17.8
57.5°	15.7
60°	13.7
62.5°	11.7
65°	10.1
67.5°	8.5
70°	7.3
72.5°	5.7
75°	4.4
77.5°	3.2
80°	2.4
82.5°	1.2
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)