

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251913

Luminaire Tested: P3AS13R209030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1006.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251913

CATALOG NUMBER: P3AS13R209030DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1251913

CATALOG NUMBER: P3AS13R209030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	773995
5°	703586
10°	519986
15°	321659
20°	183696
25°	104861
30°	58819
35°	31989
40°	17519
45°	9644
50°	5629
55°	4091
60°	3815
65°	3528
70°	3142
75°	3304
80°	2399
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9644 cd/sqm

TEST NUMBER: P1251913

CATALOG NUMBER: P3AS13R209030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.8	27.5
10°-20°	395.1	39.3
20°-30°	206.2	20.5
30°-40°	79.7	7.9
40°-50°	25.9	2.6
50°-60°	10.2	1.0
60°-70°	6.7	0.7
70°-80°	4.0	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	878.2	87.3
0°-40°	957.9	95.2
0°-60°	993.9	98.8
0°-90°	1006.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1006.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3530	
5°	3196	277
15°	1417	395
25°	433	206
35°	120	80
45°	31	26
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1251913

CATALOG NUMBER: P3AS13R209030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3529.7
1°	3522.9
2°	3481.1
3°	3417.0
4°	3317.9
5°	3196.4
6°	3052.6
7°	2893.2
8°	2708.5
9°	2528.7
10°	2335.3
12.5°	1856.2
15°	1416.9
17.5°	1060.3
20°	787.2
22.5°	583.1
25°	433.4
27.5°	319.7
30°	232.3
32.5°	168.1
35°	119.5
37.5°	86.5
40°	61.2
42.5°	43.7
45°	31.1
47.5°	22.4
50°	16.5
52.5°	12.6
55°	10.7
57.5°	9.7
60°	8.7
62.5°	7.8
65°	6.8
67.5°	5.8
70°	4.9
72.5°	4.9
75°	3.9
77.5°	2.9
80°	1.9
82.5°	1.9
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)