

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251927

Luminaire Tested: P3AS13R259030DE010 E3D1WMH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1251927  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R259030DE010 E3D1WMH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1313.0 lumens  
Efficiency: N/A  
Efficacy: 89.9 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1251927  
CATALOG NUMBER: P3AS13R259030DE010 E3D1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1251927  
 CATALOG NUMBER: P3AS13R259030DE010 E3D1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	83	83	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	77	77	77

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1437977
5°	1332090
10°	1030642
15°	492262
20°	162297
25°	68423
30°	26510
35°	11457
40°	3807
45°	1768
50°	648
55°	382
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1768 cd/sqm



TEST NUMBER: P1251927  
 CATALOG NUMBER: P3AS13R259030DE010 E3D1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	531.9	40.5
10°-20°	605.0	46.1
20°-30°	140.6	10.7
30°-40°	29.5	2.2
40°-50°	4.8	0.4
50°-60°	0.8	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1277.5	97.3
0°-40°	1307.0	99.5
0°-60°	1312.6	100.0
0°-90°	1313.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1313.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6558	
5°	6052	532
15°	2168	605
25°	283	141
35°	43	29
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1251927  
CATALOG NUMBER: P3AS13R259030DE010 E3D1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6557.7
1°	6544.4
2°	6476.3
3°	6380.6
4°	6234.5
5°	6051.7
6°	5817.0
7°	5571.3
8°	5295.7
9°	4984.8
10°	4628.7
11°	4216.0
12°	3742.3
13°	3223.4
14°	2680.7
15°	2168.4
16°	1715.2
17°	1336.3
18°	1051.1
19°	840.7
20°	695.5
21°	581.3
22°	488.0
23°	407.5
24°	340.9
25°	282.8
27.5°	167.6
30°	104.7
32.5°	67.1
35°	42.8
37.5°	25.7
40°	13.3
42.5°	8.6
45°	5.7
47.5°	3.3
50°	1.9
52.5°	1.0
55°	1.0
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.0
72.5°	0.0



TEST NUMBER: P1251927  
CATALOG NUMBER: P3AS13R259030DE010 E3D1WMH

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)