

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250728

Luminaire Tested: P3AS02R259030DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259030DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 309.9 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250728

CATALOG NUMBER: P3AS02R259030DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1250728

CATALOG NUMBER: P3AS02R259030DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	331443
5°	307395
10°	238383
15°	119547
20°	39273
25°	15606
30°	5849
35°	1686
40°	773
45°	310
50°	239
55°	191
60°	219
65°	259
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 310 cd/sqm

TEST NUMBER: P1250728

CATALOG NUMBER: P3AS02R259030DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.8	39.6
10°-20°	146.6	47.3
20°-30°	33.0	10.7
30°-40°	5.3	1.7
40°-50°	1.0	0.3
50°-60°	0.5	0.2
60°-70°	0.5	0.1
70°-80°	0.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	302.4	97.6
0°-40°	307.8	99.3
0°-60°	309.2	99.8
0°-90°	309.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	309.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1512	
5°	1396	123
15°	527	147
25°	64	33
35°	6	5
45°	1	1
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1250728

CATALOG NUMBER: P3AS02R259030DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1511.5
1°	1509.0
2°	1496.9
3°	1474.4
4°	1440.6
5°	1396.5
6°	1343.9
7°	1286.9
8°	1221.6
9°	1150.3
10°	1070.6
11°	978.8
12°	873.1
13°	762.6
14°	643.9
15°	526.6
17.5°	300.1
20°	168.3
22.5°	101.6
25°	64.5
27.5°	39.7
30°	23.1
32.5°	12.2
35°	6.3
37.5°	4.1
40°	2.7
42.5°	1.7
45°	1.0
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1250728

CATALOG NUMBER: P3AS02R259030DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)