

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250738

Luminaire Tested: P3AS02R259030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 125.0 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250738
CATALOG NUMBER: P3AS02R259030DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1250738

CATALOG NUMBER: P3AS02R259030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80191
5°	74818
10°	59919
15°	40681
20°	24619
25°	14396
30°	8204
35°	4497
40°	2405
45°	1271
50°	751
55°	535
60°	482
65°	519
70°	449
75°	424
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1271 cd/sqm



TEST NUMBER: P1250738

CATALOG NUMBER: P3AS02R259030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.2	24.1
10°-20°	49.3	39.4
20°-30°	28.2	22.5
30°-40°	11.1	8.9
40°-50°	3.4	2.7
50°-60°	1.3	1.1
60°-70°	0.9	0.7
70°-80°	0.5	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	107.6	86.1
0°-40°	118.7	94.9
0°-60°	123.4	98.7
0°-90°	125.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	125.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	366	
5°	340	30
15°	179	49
25°	60	28
35°	17	11
45°	4	3
55°	1	1
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1250738
CATALOG NUMBER: P3AS02R259030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	365.7
1°	364.9
2°	362.0
3°	356.7
4°	349.4
5°	339.9
6°	328.6
7°	316.0
8°	301.3
9°	286.2
10°	269.1
11°	252.3
12°	233.8
13°	215.5
14°	196.7
15°	179.2
17.5°	138.9
20°	105.5
22.5°	79.2
25°	59.5
27.5°	44.1
30°	32.4
32.5°	23.4
35°	16.8
37.5°	11.9
40°	8.4
42.5°	5.7
45°	4.1
47.5°	2.9
50°	2.2
52.5°	1.7
55°	1.4
57.5°	1.3
60°	1.1
62.5°	1.0
65°	1.0
67.5°	0.8
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.4
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.1



TEST NUMBER: P1250738
CATALOG NUMBER: P3AS02R259030DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)