

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251982

Luminaire Tested: P3AS13R359030DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359030DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1234.0 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251982

CATALOG NUMBER: P3AS13R359030DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1251982

CATALOG NUMBER: P3AS13R359030DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	804650
5°	788266
10°	733320
15°	537642
20°	275311
25°	99223
30°	38639
35°	13518
40°	5553
45°	1520
50°	1330
55°	1491
60°	1272
65°	986
70°	1218
75°	1610
80°	1263
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 1680 cd/sqm

TEST NUMBER: P1251982

CATALOG NUMBER: P3AS13R359030DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.8	27.1
10°-20°	626.4	50.8
20°-30°	221.8	18.0
30°-40°	38.8	3.1
40°-50°	5.7	0.5
50°-60°	3.2	0.3
60°-70°	2.2	0.2
70°-80°	1.6	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1182.0	95.8
0°-40°	1220.8	98.9
0°-60°	1229.7	99.7
0°-90°	1234.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1234.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3670	
5°	3581	334
15°	2368	626
25°	410	222
35°	50	39
45°	5	6
55°	4	3
65°	2	2
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1251982

CATALOG NUMBER: P3AS13R359030DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3669.5
1°	3668.5
2°	3656.9
3°	3634.5
4°	3614.1
5°	3581.1
6°	3547.0
7°	3509.1
8°	3462.5
9°	3389.6
10°	3293.4
11°	3160.3
12°	2999.9
13°	2809.5
14°	2599.6
15°	2368.3
17.5°	1763.8
20°	1179.8
22.5°	711.4
25°	410.1
27.5°	244.9
30°	152.6
32.5°	88.4
35°	50.5
37.5°	32.1
40°	19.4
42.5°	9.7
45°	4.9
47.5°	3.9
50°	3.9
52.5°	3.9
55°	3.9
57.5°	2.9
60°	2.9
62.5°	2.9
65°	1.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1251982
CATALOG NUMBER: P3AS13R359030DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)