

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250808

Luminaire Tested: P3AS02R359030DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359030DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 197.0 lumens
Efficiency: N/A
Efficacy: 54.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250808
CATALOG NUMBER: P3AS02R359030DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1250808
 CATALOG NUMBER: P3AS02R359030DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44996
5°	44046
10°	41260
15°	37026
20°	32203
25°	27437
30°	22991
35°	18310
40°	13253
45°	8373
50°	4571
55°	3173
60°	2982
65°	2802
70°	2629
75°	2288
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8373 cd/sqm



TEST NUMBER: P1250808
 CATALOG NUMBER: P3AS02R359030DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.6	9.5
10°-20°	45.4	23.0
20°-30°	52.0	26.4
30°-40°	42.4	21.5
40°-50°	21.4	10.9
50°-60°	7.9	4.0
60°-70°	5.3	2.7
70°-80°	3.0	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	116.0	58.9
0°-40°	158.5	80.5
0°-60°	187.8	95.3
0°-90°	197.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	197.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	205	
5°	200	19
15°	163	45
25°	113	52
35°	68	42
45°	27	21
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1250808
CATALOG NUMBER: P3AS02R359030DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	205.2
1°	205.0
2°	204.5
3°	203.5
4°	202.1
5°	200.1
6°	197.7
7°	195.2
8°	192.1
9°	188.9
10°	185.3
11°	181.4
12°	177.2
13°	172.6
14°	167.7
15°	163.1
17.5°	150.7
20°	138.0
22.5°	125.1
25°	113.4
27.5°	102.0
30°	90.8
32.5°	79.6
35°	68.4
37.5°	57.2
40°	46.3
42.5°	36.0
45°	27.0
47.5°	19.5
50°	13.4
52.5°	9.7
55°	8.3
57.5°	7.5
60°	6.8
62.5°	6.1
65°	5.4
67.5°	4.6
70°	4.1
72.5°	3.4
75°	2.7
77.5°	2.2
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.5



TEST NUMBER: P1250808
CATALOG NUMBER: P3AS02R359030DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)