

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250871

Luminaire Tested: P3AS02R459030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 272.0 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250871

CATALOG NUMBER: P3AS02R459030DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1250871

CATALOG NUMBER: P3AS02R459030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102141
5°	99758
10°	91693
15°	77708
20°	60275
25°	42148
30°	26536
35°	15633
40°	8845
45°	4311
50°	1501
55°	1223
60°	1184
65°	1141
70°	1090
75°	1017
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4311 cd/sqm

TEST NUMBER: P1250871

CATALOG NUMBER: P3AS02R459030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.9	15.4
10°-20°	94.0	34.6
20°-30°	79.8	29.3
30°-40°	38.1	14.0
40°-50°	11.5	4.2
50°-60°	2.9	1.1
60°-70°	2.2	0.8
70°-80°	1.3	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	215.7	79.3
0°-40°	253.8	93.3
0°-60°	268.2	98.6
0°-90°	272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	466	
5°	453	42
15°	342	94
25°	174	80
35°	58	38
45°	14	11
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1250871

CATALOG NUMBER: P3AS02R459030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	465.8
2.5°	462.9
5°	453.2
7.5°	436.4
10°	411.8
12.5°	379.2
15°	342.3
17.5°	301.1
20°	258.3
22.5°	214.8
25°	174.2
27.5°	137.2
30°	104.8
32.5°	78.8
35°	58.4
37.5°	43.1
40°	30.9
42.5°	21.4
45°	13.9
47.5°	7.8
50°	4.4
52.5°	3.4
55°	3.2
57.5°	2.9
60°	2.7
62.5°	2.4
65°	2.2
67.5°	1.9
70°	1.7
72.5°	1.5
75°	1.2
77.5°	1.0
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)