

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250880

Luminaire Tested: P3AS02R509030DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250880
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509030DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 338.0 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250880
CATALOG NUMBER: P3AS02R509030DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1250880

CATALOG NUMBER: P3AS02R509030DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	95	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	67	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118127
5°	114968
10°	109706
15°	99320
20°	85921
25°	70480
30°	40487
35°	12582
40°	3378
45°	1178
50°	273
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1178 cd/sqm



TEST NUMBER: P1250880
 CATALOG NUMBER: P3AS02R509030DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.9	14.5
10°-20°	121.2	35.9
20°-30°	127.4	37.7
30°-40°	36.5	10.8
40°-50°	3.6	1.1
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	297.6	88.0
0°-40°	334.0	98.8
0°-60°	337.9	100.0
0°-90°	338.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	338.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	539	
5°	522	49
15°	438	121
25°	291	127
35°	47	36
45°	4	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1250880
CATALOG NUMBER: P3AS02R509030DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	538.7
1°	537.8
2°	535.4
3°	532.0
4°	527.3
5°	522.3
6°	517.0
7°	511.2
8°	505.9
9°	499.7
10°	492.7
11°	484.8
12°	475.6
13°	464.1
14°	451.7
15°	437.5
16°	422.5
17°	408.0
18°	393.1
19°	379.9
20°	368.2
21°	357.0
22°	344.3
23°	329.6
24°	312.4
25°	291.3
26°	268.4
27°	242.9
28°	217.5
29°	190.1
30°	159.9
31°	131.7
32°	105.7
32.5°	94.3
33°	82.9
34°	63.6
35°	47.0
36°	34.5
37°	25.6
37.5°	22.2
38°	19.2
39°	14.9
40°	11.8
42.5°	6.7
45°	3.8



TEST NUMBER: P1250880
CATALOG NUMBER: P3AS02R509030DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.1
50°	0.8
52.5°	0.4
55°	0.2
57.5°	0.2
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)