

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250890

Luminaire Tested: P3AS02R509030DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509030DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 105.0 lumens
Efficiency: N/A
Efficacy: 29.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250890

CATALOG NUMBER: P3AS02R509030DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1250890

CATALOG NUMBER: P3AS02R509030DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21336
5°	21021
10°	20084
15°	18615
20°	16731
25°	14711
30°	12508
35°	10146
40°	7614
45°	4900
50°	2320
55°	1835
60°	1754
65°	1608
70°	1475
75°	1356
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4900 cd/sqm

TEST NUMBER: P1250890

CATALOG NUMBER: P3AS02R509030DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.0	8.5
10°-20°	22.9	21.8
20°-30°	27.8	26.5
30°-40°	23.5	22.4
40°-50°	12.2	11.6
50°-60°	4.4	4.2
60°-70°	3.1	2.9
70°-80°	1.7	1.6
80°-90°	0.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	59.6	56.7
0°-40°	83.1	79.2
0°-60°	99.8	95.0
0°-90°	105.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	105.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	97	
5°	96	9
15°	82	23
25°	61	28
35°	38	24
45°	16	12
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1250890

CATALOG NUMBER: P3AS02R509030DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	97.3
2.5°	96.9
5°	95.5
7.5°	93.4
10°	90.2
12.5°	86.3
15°	82.0
17.5°	77.1
20°	71.7
22.5°	66.2
25°	60.8
27.5°	55.1
30°	49.4
32.5°	43.6
35°	37.9
37.5°	32.2
40°	26.6
42.5°	21.2
45°	15.8
47.5°	10.5
50°	6.8
52.5°	5.3
55°	4.8
57.5°	4.3
60°	4.0
62.5°	3.5
65°	3.1
67.5°	2.6
70°	2.3
72.5°	1.9
75°	1.6
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)