

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250901

Luminaire Tested: P3AS02R509030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 179.9 lumens
Efficiency: N/A
Efficacy: 50.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250901

CATALOG NUMBER: P3AS02R509030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250901

CATALOG NUMBER: P3AS02R509030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		79
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		73
5	91	83	77	72	90	82	76	72	80	75	71		78	74	70		68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		53
10	71	62	56	52	70	61	55	52	60	55	51		59	55	51		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52342
5°	50935
10°	46982
15°	41317
20°	34560
25°	27413
30°	20104
35°	13813
40°	8788
45°	4900
50°	2661
55°	2217
60°	1930
65°	1764
70°	1539
75°	1440
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4900 cd/sqm

TEST NUMBER: P1250901

CATALOG NUMBER: P3AS02R509030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.4	11.9
10°-20°	50.4	28.0
20°-30°	51.5	28.6
30°-40°	32.7	18.2
40°-50°	13.0	7.2
50°-60°	5.3	2.9
60°-70°	3.4	1.9
70°-80°	1.7	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	123.4	68.6
0°-40°	156.1	86.7
0°-60°	174.3	96.9
0°-90°	179.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	179.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	239	
5°	231	21
15°	182	50
25°	113	52
35°	52	33
45°	16	13
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1250901

CATALOG NUMBER: P3AS02R509030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	238.7
2.5°	237.0
5°	231.4
7.5°	222.7
10°	211.0
12.5°	197.1
15°	182.0
17.5°	165.4
20°	148.1
22.5°	130.8
25°	113.3
27.5°	95.7
30°	79.4
32.5°	64.8
35°	51.6
37.5°	40.4
40°	30.7
42.5°	22.7
45°	15.8
47.5°	10.7
50°	7.8
52.5°	6.6
55°	5.8
57.5°	5.1
60°	4.4
62.5°	3.9
65°	3.4
67.5°	2.9
70°	2.4
72.5°	1.9
75°	1.7
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)