

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252031

Luminaire Tested: P3AS13R409030DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409030DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 868.0 lumens
Efficiency: N/A
Efficacy: 59.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252031
CATALOG NUMBER: P3AS13R409030DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1252031
 CATALOG NUMBER: P3AS13R409030DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194853
5°	191327
10°	180335
15°	163792
20°	143909
25°	122886
30°	101788
35°	78514
40°	55876
45°	37647
50°	20537
55°	14489
60°	13639
65°	12608
70°	11220
75°	10675
80°	8587
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37647 cd/sqm



TEST NUMBER: P1252031

CATALOG NUMBER: P3AS13R409030DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.1	9.3
10°-20°	201.0	23.2
20°-30°	232.4	26.8
30°-40°	183.1	21.1
40°-50°	94.0	10.8
50°-60°	35.9	4.1
60°-70°	23.8	2.7
70°-80°	12.9	1.5
80°-90°	3.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.4	59.3
0°-40°	697.5	80.4
0°-60°	827.5	95.3
0°-90°	868.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	868.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	889	
5°	869	81
15°	722	201
25°	508	232
35°	293	183
45°	121	94
55°	38	36
65°	24	24
75°	13	13
85°	3	4
90°	0	



TEST NUMBER: P1252031
CATALOG NUMBER: P3AS13R409030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	888.6
2.5°	883.7
5°	869.2
7.5°	843.9
10°	809.9
12.5°	770.1
15°	721.5
17.5°	671.0
20°	616.7
22.5°	561.3
25°	507.9
27.5°	454.5
30°	402.0
32.5°	348.6
35°	293.3
37.5°	241.8
40°	195.2
42.5°	155.4
45°	121.4
47.5°	88.4
50°	60.2
52.5°	43.7
55°	37.9
57.5°	34.0
60°	31.1
62.5°	27.2
65°	24.3
67.5°	20.4
70°	17.5
72.5°	14.6
75°	12.6
77.5°	9.7
80°	6.8
82.5°	5.8
85°	2.9
87.5°	1.9
90°	0.0

(END OF REPORT)