

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252034

Luminaire Tested: P3AS13R409030DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409030DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 714.0 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252034

CATALOG NUMBER: P3AS13R409030DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1252034

CATALOG NUMBER: P3AS13R409030DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	222329
5°	217829
10°	202802
15°	176755
20°	142462
25°	106772
30°	75075
35°	49175
40°	29770
45°	17800
50°	10609
55°	8564
60°	7675
65°	6538
70°	6219
75°	4914
80°	4925
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17800 cd/sqm

TEST NUMBER: P1252034

CATALOG NUMBER: P3AS13R409030DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.9	12.9
10°-20°	214.5	30.0
20°-30°	202.1	28.3
30°-40°	116.9	16.4
40°-50°	46.6	6.5
50°-60°	20.6	2.9
60°-70°	12.7	1.8
70°-80°	6.7	0.9
80°-90°	2.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.4	71.2
0°-40°	625.3	87.6
0°-60°	692.5	97.0
0°-90°	714.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	714.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1014	
5°	990	92
15°	779	214
25°	441	202
35°	184	117
45°	57	47
55°	22	21
65°	13	13
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1252034

CATALOG NUMBER: P3AS13R409030DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1013.9
2.5°	1008.0
5°	989.6
7.5°	955.5
10°	910.8
12.5°	850.6
15°	778.6
17.5°	697.9
20°	610.5
22.5°	523.0
25°	441.3
27.5°	365.5
30°	296.5
32.5°	236.2
35°	183.7
37.5°	139.0
40°	104.0
42.5°	77.8
45°	57.4
47.5°	41.8
50°	31.1
52.5°	25.3
55°	22.4
57.5°	20.4
60°	17.5
62.5°	14.6
65°	12.6
67.5°	10.7
70°	9.7
72.5°	7.8
75°	5.8
77.5°	4.9
80°	3.9
82.5°	2.9
85°	1.9
87.5°	1.0
90°	0.0

(END OF REPORT)