

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250932

Luminaire Tested: P3AS02R609030DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609030DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 314.9 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250932

CATALOG NUMBER: P3AS02R609030DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1250932

CATALOG NUMBER: P3AS02R609030DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75213
5°	72243
10°	74370
15°	75324
20°	66506
25°	56060
30°	45475
35°	29607
40°	13597
45°	5210
50°	1740
55°	459
60°	439
65°	363
70°	321
75°	424
80°	253
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5210 cd/sqm

TEST NUMBER: P1250932

CATALOG NUMBER: P3AS02R609030DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.6	10.0
10°-20°	90.9	28.9
20°-30°	106.0	33.7
30°-40°	68.4	21.7
40°-50°	15.3	4.9
50°-60°	1.5	0.5
60°-70°	0.7	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.4	72.5
0°-40°	296.8	94.3
0°-60°	313.7	99.6
0°-90°	314.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	314.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	343	
5°	328	32
15°	332	91
25°	232	106
35°	111	68
45°	17	15
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1250932

CATALOG NUMBER: P3AS02R609030DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	343.0
2.5°	337.4
5°	328.2
7.5°	327.7
10°	334.0
12.5°	338.2
15°	331.8
17.5°	312.8
20°	285.0
22.5°	256.1
25°	231.7
27.5°	207.8
30°	179.6
32.5°	146.4
35°	110.6
37.5°	75.5
40°	47.5
42.5°	28.5
45°	16.8
47.5°	9.7
50°	5.1
52.5°	1.7
55°	1.2
57.5°	1.0
60°	1.0
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)