

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252061

Luminaire Tested: P3AS13R459030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1086.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252061

CATALOG NUMBER: P3AS13R459030DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1252061

CATALOG NUMBER: P3AS13R459030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90	88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75	74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61	59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407840
5°	398282
10°	366103
15°	310217
20°	240681
25°	168252
30°	105991
35°	62399
40°	35295
45°	17180
50°	5970
55°	4817
60°	4693
65°	4514
70°	4360
75°	4151
80°	3662
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17180 cd/sqm

TEST NUMBER: P1252061

CATALOG NUMBER: P3AS13R459030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.5	15.4
10°-20°	375.3	34.6
20°-30°	318.7	29.3
30°-40°	152.0	14.0
40°-50°	45.8	4.2
50°-60°	11.6	1.1
60°-70°	8.6	0.8
70°-80°	5.1	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	861.4	79.3
0°-40°	1013.4	93.3
0°-60°	1070.8	98.6
0°-90°	1086.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1086.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1860	
5°	1809	167
15°	1366	375
25°	695	319
35°	233	152
45°	55	46
55°	13	12
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1252061

CATALOG NUMBER: P3AS13R459030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1859.9
2.5°	1848.2
5°	1809.4
7.5°	1742.3
10°	1644.2
12.5°	1514.1
15°	1366.5
17.5°	1202.4
20°	1031.4
22.5°	857.6
25°	695.4
27.5°	547.8
30°	418.6
32.5°	314.7
35°	233.1
37.5°	171.9
40°	123.3
42.5°	85.5
45°	55.4
47.5°	31.1
50°	17.5
52.5°	13.6
55°	12.6
57.5°	11.7
60°	10.7
62.5°	9.7
65°	8.7
67.5°	7.8
70°	6.8
72.5°	5.8
75°	4.9
77.5°	3.9
80°	2.9
82.5°	1.9
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)